



Solvent Recovery Distiller
Unit

ASPHALT

www.testmak.com





Solvent Recovery Distiller Unit



PRODUCT MODEL

| B1810 | Solvent Recovery Distiller Unit, 220-240 V 50-60 Hz | |
|-----------|---|--|
| B1810/110 | Solvent Recovery Distiller Unit, 110 V 60 Hz | |

INFORMATION

| Manufacturer | TESTMAK INS.LAB.MAK.SAN.VE TİC. PAZ. ITH. IHR. LTD. STI | |
|--------------------------|---|--|
| Country of Origin | n TURKEY | |
| Product name | Solvent Recovery Distiller Unit | |



Telephone: +90 312 395 36 42

Fax : +90 312 395 36 01

Website : www.testmak.com E-Mail : info@testmak.com





Solvent Recovery Distiller Unit

DESCRIPTION

The Solvent Recovery Distiller Unit is used to recover the solvent liquid after its use for the extraction tests. This recovery unit has been designed to recover unflammable solvents. The consists of two stainless steel chambers. The first chamber is used for dirty solvent. The second chamber used for cleaned solvent. ASolvent in the left-hand side chamber is distilled by an electrical heater and then passes through a water cooling system and drops into the second chamber ready for re-use a test. Once the process is completed, a temperature switch automatically stops the heating elements. The solvent recovery unit is supplied complete with 10 m plastic tubing, tube clamps, sieve insert 0.6 mm opening and one lid.

The Solvent Recovery Unit is supplied complete with;

- Plastic Tubing, 10 m
- Tube Clamps
- Sieve Insert, 0.6 mm
- Lid

TECHNICAL SPECIFICATIONS

| Product Code | B1810 |
|-----------------|----------------|
| Max. Tempature | 150°C |
| Dimensions | 420x350x680 mm |
| Weight (approx) | 20 kg |
| Power | 1200 W |



Telephone: +90 312 395 36 42 Website: www.testmak.com
Fax : +90 312 395 36 01 E-Mail : info@testmak.com





Telephone: +90 312 395 36 42 Fax: +90 312 395 36 01 Website: www.testmak.com E-Mail: info@testmak.com Koca Sinan Industrial Sites 1183 Street No: 40 06370 OSTIM / ANKARA / TURKEY